

Prüfstecker Drehfeld-Control

Bestellnr. 1436



- nach VDE 0413, Teil 7, DIN-EN 61557-7

Technische Daten

Ampere	63 A
Pole	4 p
Volt	400 V
Uhrzeitstellung	6 h
Hertz	50-60 Hz
Kontakt	standard
Schutzart	IP 44
Gewicht	612 g
Prüfzeichen	CQC

Abmessungen



Zeichnung 2 MB 140	Amp. Pole	16		32		63	
		4	5	4	5	4	5
Maße in mm	a	126	129	145	145	211	211
	b	60	65	66	74	100	100
	h	62	69	71	80	100	100
	n	90	93	99	99	145	145